COOLING TOWER				EVAPCO, INC. evapeo					AX142417-DR	A-ST	REV.
MODEL #	(S 14-19L24	SCALE		EVAPCO	, TIAC	1	<b>P</b>	SERIAL #			DATE 12/8/2025
2. HEAVIEST S 3. MPT DENOTE FPT DENOTE BFW DENOTE GVD DENOTE 4. +UNIT WEIG ACCESSORI 5. MAKE-UP W. 20 psi MIN [1 6. 3/4" DIA. MO RECOMMEN	TOR LOCATION ECTION IS UPPER SECTIC ES MALE PIPE THREAD ES FEMALE PIPE THREAD ES BEVELED FOR WELDIN ES GROOVED HT DOES NOT INCLUDE ES (SEE ACCESSORY DRA ATER PRESSURE 37 kPa], 50 psi MAX [344 kF UNTING HOLES. REFER TO DED STEEL SUPPORT DRA S LISTED AS FOLLOWS: EN	ng Awings) Pa] O Awing.		FACE B PLAN VIEW	7-11 5/8" 124 ] 9 5/8" 245 ]	0 0 0  0	FACE C ACCESS DOOR			<b>(2)</b> 1	<b>ACE D</b> .0" [250] ASME BOLT PATTERN T
			7" [ 178	17			FACE A				
				9'-4 3/8" 2855 ]			<u> </u>	 )	)	∕− 4" [1( OVER	00] FPT FLOW
				19 <sup>1</sup> -4" [ 5893 ]						— 3" [80 MAKE	)] MPT -UP
				9'-11 5/8" 3038 ]			ACCESS DOOR			— 4" [10 DRAII	00] FPT N
				<u> </u>	<b>,</b>		م و				
	13'- [ 424 FACI	11 1/4" 8 ] <b>E B</b>		3/8" [ 10 ] 2'-5 3/4" _ [ 756 ] 1'-11 7/8" _ [ 606 ] 9 1/2 [ 241 ] 3 [ 98	7/8" _	14" [350	] BFW/GVD —   -   -   -   -   -   -   -   -   -	[ 3	10'-3" 3124 ] 11'-1" 3378 ] 4 1/2"		
SHIPPING WEIGHT	21260 lbs+ [9645] kg	+	OPERATING WEIGHT	47900 lbs+ [21730] kg+	HEAVIE W	EST SECTION VEIGHT	11900 lbs+ [5400] kg+	NO. O	F SHIPPING SECTIONS	2	DRAWN BY: AWT