UNIT CONDENSER	EVADOO TI	NC evapeo	DWG. # WV030606-DRC-ST	REV.
MODEL # LRC-38 SCALE NTS	EVAPCO, II	NC.	SERIAL #	DATE _{11/26/2025}
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm] 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPIN 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX	FACE B 3'-4 1/2" PLAN VIEW	FACE C 10'-1 7/8" [3096] FACE A		FACE D
1'-8 1/4" *			_	
3 1/4" TYP 2" [50] MPT OVERFLOW 2" [50] MPT DRAIN	6'-7 3/4" [2026] 3'-1/4" * [919] 8 3/4" [222] 5/8" 1'-1 1/8"	ACCESS DOOR [5'-6" [1676] [10'-1.7/8" [3096] [TACE A	1" [25] MPT MAKE-UP	5'-3 3/8" [1610] 1'-8 1/8" [511]
SHIPPING	PERATING 3710 lbs+ [1685] kg+ WEIGHT	HEAVIEST SECTION 2650 lbs+ [1205] kg+	NO. OF SHIPPING SECTIONS 1	RAWN BY: TLS