UNIT CONDENSER			EVADA	AT AS	IC ev	apeo	DWG. # WV050906-DRC-ST	REV.
MODEL #	_RC-116	SCALE NTS	EVAPO	JO, IN	VC.	<b>1</b>	SERIAL #	DATE <sub>11/26/2025</sub>
FPT DENOTES BFW DENOTE GVD DENOTES FLG DENOTES PE DENOTES 3. +UNIT WEIGH	S MALE PIPE THREAD S FEMALE PIPE THREAD S BEVELED FOR WELDI S GROOVED S FLANGE PLAIN END T DOES NOT INCLUDE	ING			********	FACE C		
4. 3/4" [19mm] DI RECOMMEND 5. DIMENSIONS I 6. * - APPROXIM/ USE FOR PRE 7. MAKE-UP WA	ATE DIMENSIONS DO NO -FABRICATION OF CON	REFER TO RAWING ENGLISH FT IN METRIC] [mm] OT NECTING PIP	FACE B 5'-5/	8"]				FACE D
			1			15'-2 1/4" [ 4629 ] FACE A		
-•	2'-6 3/8" *						[ 1905 ]	-
4" [100] PE – REFRIG IN 4" [100] PE – REFRIG OUT		1'-7	3'-7 1/2" [1106] 195] * 6'-7 3/4" [2026]		A	CCESS		6'-7 3/4" [ 2026 ]
3 1/4" [83] TYP. →		(1)	3'-1/4" [ 919 ]			DOOR		1'-8 1/8"
3" [80] MPT — OVERFLOW		4	2 5/8"	-		8'-5 3/8" [ 2575 ]	└─ 1" [25] MPT MAKE-UP	ACCESS DOOR
2" [50] MPT — DRAIN	5'-5/8" [ 1540 ] FACE B	1'-8 7/8" [ 530 ]	1'-1	5/8" 46 ]		15'-2 1/4" [ 4629 ] <b>FACE A</b>		
SHIPPING WEIGHT	5290 lbs+ [2400] kg	]+	OPERATING 8100 lbs+ [36]	75] kg+	HEAVIEST SECTION WEIGHT	5290 lbs+ [2400] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: TLS