UNIT CONDENSER	EVADOO T	NC evapco °	DWG. # WV050910-DRC-ST	REV
MODEL # LRC-174 SCALE NT:	T EVAPCO, I	NC. evapco	SERIAL #	DATE <sub>11/26/2025</sub>
NOTES:  1. (M)- FAN MOTOR LOCATION  2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES PLANGE PE DENOTES PLAIN END  3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)  4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING  5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH F [METRIC]]  6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING  7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX	nm] <b>FACE B</b> 5'-5/8"	FACE C		FACE D
2'-6 3/8" * [ 770 ] *  4" [100] PE REFRIG IN		15'-2 1/4" [ 4629 ] FACE A	6'-3" [ 1905 ]	
A" [100] PE REFRIG OUT	2'-10 1/2" * [ 1487 ]			6'-7 3/4" [ 2026 ]
3 1/4" TYP	5 1/4" *   3'-1/4" [919]	ACCESS DOOR		1'-8 1/8" [ 511 ]
3" [80] MPT OVERFLOW 2" [50] MPT DRAIN 1'-8 7/8" [ 530 ]	2 5/8"	8'-5 3/8" [ 2575 ]	1" [25] MPT MAKE-UP	ACCESS DOOR
5'-5/8" [ 1540 ] FACE B	1'-1 5/8"			
SHIPPING 7090 lbs+ [3220] kg+ WEIGHT	OPERATING 10030 lbs+ [4550] kg+	HEAVIEST SECTION 7090 lbs+ [3220] kg+	NO. OF SHIPPING SECTIONS 1	RAWN BY: TLS