UNIT	NDENSER	EVAD	CO TNI	eva	<b>pco</b>	VG. # WV080910-DRD-ST	REV
MODEL # LRC-269	SCALE NTS	T EVAP	CO, IN	C.	SEI	RIAL #	DATE <sub>11/26/2025</sub>
4. 3/4" [19mm] DIA. MOUN RECOMMENDED STEE 5. DIMENSIONS LISTED A 6. * - APPROXIMATE DIMI	PIPE THREAD E PIPE THREAD ED FOR WELDING //ED E NOT INCLUDE CCESSORY DRAWINGS) TING HOLES. REFER TO L SUPPORT DRAWING S FOLLOWS: ENGLISH FT [METRIC] [m ENSIONS DO NOT ATION OF CONNECTING F SSURE	m]	FACE B [7'-10"] /IEW		FACE C  15'-21 [ 4625] FACE A		FACE D
(2) 4" [100] PE REFRIG IN		<u> </u>			6	[ 1905 ]	
(2) 4" [100] PE — REFRIG OUT		2'-10 1/2" * [ 1583 ] [ 876 ] * - 7" - *	8'-2 1/2" [ 2502 ]		ACCESS - X		6'-7 3/4" [ 2026 ]
3 1/4" TYP		[ 178 ]   3'-1/4" [ 919 ]   (P)   (P	•		DOOR	1101/01	
3" [80] MPT OVERFLOW	4 1/4	2 5/8"		-	8'-5 <u>3/</u> 8"	1'-8 1/8" [511] 2" [50] MPT MAKE-UP	ACCESS DOOR
2" [50] MPT DRAIN	7'-10" [86] [2388]	10" 	1'-3 7/8" [ 405 ]		15'-2 1 [ 4629 <b>FACE A</b>		
SHIPPING 10 WEIGHT	860 lbs+ [4930] kg+	OPERATING 15810 lbs+ [7	7175] kg+	AVIEST SECTION WEIGHT	10860 lbs+ [4930] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: TLS