UNIT	CONDENSE	₹
MODEL #	LRC-379	SCALE NTS


EVAPCO, INC. Evapeo


DWG. # REV. WV081212-DRD-ST DATE<sub>11/26/2025</sub> SERIAL #


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
- 6. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX

## **FACE C**







**SHIPPING** WEIGHT

DRAIN

14800 lbs+ [6715] kg+

7'-10" [ 2388 ]

**FACE B** 

OPERATING WEIGHT

21500 lbs+ [9755] kg+

HEAVIEST SECTION WEIGHT

14800 lbs+ [6715] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: