



# EVAPCO, INC.




|                       |           |        |                 |      |           |          |
|-----------------------|-----------|--------|-----------------|------|-----------|----------|
| UNIT                  | MODEL #   | SCALE  | DWG. #          | REV. | DATE      | SERIAL # |
| EVAPORATIVE CONDENSER | PMC-1985E | N.T.S. | CE124012-DRB-ST | -    | 7/20/2025 |          |

- NOTES:
- (M)- FAN MOTOR LOCATION
  - HEAVIEST SECTION IS UPPER SECTION
  - MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING
  - +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
  - 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
  - MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
  - \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
  - DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm]

**FACE 1  
PLAN VIEW**



**FACE 1**



**FACE 2**

|                 |                        |                  |                        |                         |                        |                          |   |
|-----------------|------------------------|------------------|------------------------|-------------------------|------------------------|--------------------------|---|
| SHIPPING WEIGHT | 73590 lbs+ [33380] kg+ | OPERATING WEIGHT | 93880 lbs+ [42583] kg+ | HEAVIEST SECTION WEIGHT | 29050 lbs+ [13177] kg+ | NO. OF SHIPPING SECTIONS | 3 |
|-----------------|------------------------|------------------|------------------------|-------------------------|------------------------|--------------------------|---|