EVAPCO, INC. UNIT MODEL # SERIAL # TLE041236-DRA-ST N.T.S. **COOLING TOWER** LSTE-4212U 12/14/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING 4'-5/8" [1234] GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 1 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO **PLAN VIEW** RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN (M)[METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 7 5/8" FROM CONNECTION END OF UNIT 11'-11 1/2" [3645] FACE 2 10 1/2 ₋ [267] 6 [150] BFW/GVD **INLET** 74 7/8 [1902] (2) ACCESS DOORS 9'-10 3/8" [3007] √ 3 [80] MPT **OVERFLOW** 20 1/8 _. [511] 1 [25] MPT -2 [50] MPT MAKE-UP DRAIN 43 1/2 [1105] 26 1/8 (M)(M)[664] 11 7/8 **-** [302] 6 [152] 15 3/4 [400] 6 [150] BFW/GVD 3 [76] OUTLET 20 7/8 [530] 1 3/4 [44] 19 1/8 [486] 11'-11 1/2" 4'-5/8" [3645] FACE 2 FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 3240 lbs+ [1470] kg+ 4550 lbs+ [2064] kg+ 1860 lbs+ [844] kg+ 2 WEIGHT WEIGHT WEIGHT