## EVAPCO, INC.



UNIT MODEL # SERIAL # TLEO51248-DRA-ST N.T.S. **COOLING TOWER** LSTE-5412L 12/13/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING 5'-5" [ 1652 ] GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 1 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 33" 11'-11 1/2" FROM CONNECTION END OF UNIT 3645] FACE 2 10 1/2 3 [ 76 ] 6 [150] BFW/GVD INLET 89 5/8 [ 2277 ] 12'-6 3/4" [ 3829 ] (2) ACCESS DOOR 3 [80] MPT 1 [25] MPT **OVERFLOW** MAKE-UP 2 [50] MPT 61 1/8 [ 1553 ] DRAIN 26 1/4 **M** [ 667 ] 6 1/4 [ 159 ] 3 [ 76 ] 18 3/4 [ 476 ] 16 1/8 1 3/4 11'-11 1/2" [ 410 ] [ 3645 ] 26 1/8 FACE 2 [ 664 ] 6 [150] BFW/GVD 32 3/8 OUTLET [ 822 ] 19 [ 483 ] [ 1652 ] FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 4690 lbs+ [2127] kg+ 6810 lbs+ [3089] kg+ 2700 lbs+ [1225] kg+ 2 WEIGHT WEIGHT WEIGHT