EVAPCO, INC. UNIT MODEL # SERIAL # HCD142610-DRC-ST PHC-D790 **EVAPORATIVE CONDENSER** 11/26/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" DIA. MOUNTING HOLES. REFER TO 13'-11" **FACE 2** [4242] RECOMMENDED STEEL SUPPORT DRAWING. **PLAN VIEW** 7. *- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTION PIPING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] FACE 1 9 1/2 * [241] INTERIOR PAN CONNECTIONS THIS SIDE 4 1/8 105] (2) 4 [100] BFW -REFRIG IN 44 3/4 * [1137] 96 1/2 [2451] (2)1/2 [15] BFW **PURGE** 27 3/8 * [695] 18'-2 5/8" [5553] 122 1/8 (2) 4 [100] BFW **ACCESS** [3102] **RÉFRIG OUT** DOOR TYP BOTH SIDES **INTERIOR PAN** 26'-0" [7925] FACE 2 CONNECTIONS THIS SIDE FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: HEAVIEST SECTION TLS 33160 lbs+ [15045] kg+ 53720 lbs+ [24370] kg+ 21660 lbs+ [9825] kg+ WEIGHT WEIGHT WEIGHT