EVAPCO, INC.

UNIT MODEL # SERIAL # N.T.S. TLEOP1224-DRA-ST **COOLING TOWER** LSTE-8P112U 12/15/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE 7'-10" [2388] ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 11'-11 3/4" [3651] FACE 2 7/8 [21] 94 [2388] 71 7/8 [1826] 11 3/8 ∠8 [200] BFW/GVD 290] **INLET** 62 7/8 [1596] (2) ACCESS DOOR -12'-6 1/4" [3816] 3 [80] MPT **OVERFLOW** 2 [50] MPT MÅKE-UP 87 3/8 [2219] 35 1/2 [902] · 2 [50] MPT 21 3/8 [543] DRAIN 11'-11 3/4" [3651] 7 5/8 2 1/2 [63] [194] 3 1/8 [79] 23 5/8 FACE 2 [178] [600] 40 3/8 8 [200] BFW/GVD 1026 44 3/8 [1127] OUTLET 7'-10" [2388]

SHIPPING WEIGHT

5710 lbs+ [2590] kg+

OPERATING WEIGHT

FACE 1

9190 lbs+ [4169] kg+

HEAVIEST SECTION WEIGHT

3590 lbs+ [1628] kg+

NO. OF SHIPPING SECTIONS

2