EVAPCO, INC. UNIT MODEL # SERIAL # N.T.S. TLEOP1824-DRA-ST **COOLING TOWER** LSTE-8P118U 12/14/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE 7'-10" **FACE 1** [2388] ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 18'-0" [5486] FACE 2 7/8 [21] 94 [2388] 108 [2743] 11 3/8 ∠8 [200] BFW/GVD 290] **INLET** 62 7/8 [1596] (2) ACCESS DOOR -12'-6 1/4" [3816] 3 [80] MPT 2 [50] MPT **OVERFLOW** MAKE-UP 87 3/8 [2219] 35 1/2 [902] 2 [50] MP 21 3/8 [543] DRAIN 7 5/8 18'-0" [5486] 2 1/2 [194] 3 1/8 [79] 23 5/8 FACE 2 [178] 600 40 3/8 [1026 8 [200] BFW/GVD 44 3/8 [1127] **OUTLET** 7'-10" [2388] FACE 1

HEAVIEST SECTION

WEIGHT

5220 lbs+ [2368] kg+

NO. OF SHIPPING SECTIONS

2

SHIPPING

WEIGHT

8190 lbs+ [3715] kg+

OPERATING

WEIGHT

13540 lbs+ [6142] kg+