COOLING TOWER			EVI	NDCO I		/apco	wg. # AX122217-DRA	# AX122217-DRA-ST REV	
MODEL #	AXS 12-19I22	SCALE] EVA	APCO, I	YC.	SE	ERIAL #	DATE 12/10/2025	
2. HEAVIEST 3. MPT DENG FPT DENG BFW DEN GVD DENG 4. +UNIT WE ACCESSO 5. MAKE-UP 20 psi MIN 6. 3/4" DIA. N RECOMMI	MOTOR LOCATION SECTION IS UPPER SECTOTES MALE PIPE THREAD DITES FEMALE PIPE THREAD OTES BEVELED FOR WEL OTES GROOVED IGHT DOES NOT INCLUDE RIES (SEE ACCESSORY D WATER PRESSURE [137 kPa], 50 psi MAX [344 MOUNTING HOLES. REFER ENDED STEEL SUPPORT I INS LISTED AS FOLLOWS:	AD DING : RAWINGS) kPa] TO DRAWING.		FACE B PLAN VIEW	5'-11" 1804] V	FACE C ACCESS DOOR		FACE D (2) 8" [200] ASME 150 FLG PATTERN INLET	
			7" [178]			FACE A			
			9'-4 3/8" [2855] 19'-4	[1]		(÷	<u> </u>	4" [100] FPT OVERFLOW	
			9'-11 5/8"	<u>•</u>	y y	ACCESS DOOR		3" [80] MPT MAKE-UP 4" [100] FPT DRAIN	
		11'-10" 3607] <u>FACE</u>	3/8" [10]	3 7/8"		[300] BFW/GVD OUTLET 22'-9" [6934]	9'-3" [2819] 10'-1" [3073] — 11'-4 1/2" [3467]		
SHIPPING WEIGHT	16410 lbs+ [7445] l	kg+	OPERATING WEIGHT 37350 lb:	s+ [16945] kg+	HEAVIEST SECTION WEIGHT	9220 lbs+ [4185] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY: JLM	