UNIT CONDENSER	EVADOO TI	NC evapco	DWG. # WV030604-DRC-ST	REV.
MODEL # LRC-27 SCALE NTS	EVAPCO, II	NC.	SERIAL #	DATE <sub>11/26/2025</sub>
NOTES:  1. (M)- FAN MOTOR LOCATION  2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END  3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)  4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING  5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]  6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPIN  7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX	FACE B 3'-4 1/2" [ 1029 ]	FACE C  10'-1 7/8" [ 3096 ]  FACE A		FACE D
4" [100] PE REFRIG IN 4" [100] PE REFRIG OUT [ 305 ] 2" [50] MPT OVERFLOW 2" [50] MPT DRAIN	6'-7 3/4" [2026] 1'-3/4" * [324] * 3'-1/4" [919] 8 3/4" [222]	ACCESS DOOR [5'-6" [10'-1 7/8" [3096]]  FACE A	ACCESS DOOR  1" [25] MPT MAKE-UP	5'-3 3/8" [ 1610 ] 1'-8 1/8" [ 511 ]
SHIPPING 2320 lbs+ [1055] kg+	PERATING 3360 lbs+ [1525] kg+	HEAVIEST SECTION 2320 lbs+ [1055] kg+	NO. OF SHIPPING SECTIONS	RAWN BY: TLS