UNIT CONDENSER		EVADOO T	NC evapco	DWG. # WV080908-DRD-ST	REV.
MODEL #	LRC-240 SCALE NTS	EVAPCO, I	NC.	SERIAL #	DATE 1/26/2025
FPT DENOTES BFW DENOTES GVD DENOTES FLG DENOTES PE DENOTES PE DENOTES 3. +UNIT WEIGHT ACCESSORIES 4. 3/4" [19mm] DIA RECOMMENDE 5. DIMENSIONS L 6. * - APPROXIMA USE FOR PRE- 7. MAKE-UP WAT 20 psi [137 kPa]	MALE PIPE THREAD FEMALE PIPE THREAD S BEVELED FOR WELDING GROOVED FLANGE PLAIN END DOES NOT INCLUDE (SEE ACCESSORY DRAWINGS) A MOUNTING HOLES. REFER TO D STEEL SUPPORT DRAWING ISTED AS FOLLOWS: ENGLISH F [METRIC] [I TE DIMENSIONS DO NOT FABRICATION OF CONNECTING ER PRESSURE MIN, 50 psi [344 kPa] MAX	mm] 7'-10" [ 2388 ]	FACE C		FACE D
2'-1/2" * - [ 622 ] * - (2) 4" [100] PE	3'-8 7/8" * -			[ 6'-3" ]	
(2) 4" [100] PE - REFRIG OUT		2'-3" * [1392] [686] * 7'-7" [2311]			6'-7 3/4" [ 2026 ]
3 1/4" TYP		(*)	ACCESS DOOR 8'-5 3/8" [2575]	1'-8 1/8" [511]	
3" [80] MPT — OVERFLOW		(4°		2" [50] MPT MAKF-UP	ACCESS DOOR
2" [50] MPT — DRAIN	7'-10" [ 2388 ]	'-10" 864 ]	15'-2	2 1/4"	DOOK
FACE A  FACE B					
SHIPPING WEIGHT	9340 lbs+ [4240] kg+	OPERATING 14070 lbs+ [6385] kg+ WEIGHT	HEAVIEST SECTION 9340 lbs+ [4240] kg+ WEIGHT	NO. OF SHIPPING SECTIONS 1	DRAWN BY: TLS