


UNIT	CONDENSER		EVAPCO, INC. 	DWG. #	EG092410-DRC-ST	REV.
MODEL #	eco-ATC-812A	SCALE NTS		SERIAL #		DATE 1/24/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]



FACE B



FACE A

SHIPPING WEIGHT 32880 lbs+ [14915] kg+ OPERATING WEIGHT 41480 lbs+ [18820] kg+ HEAVIEST SECTION WEIGHT 14570 lbs+ [6610] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: TLM