



# EVAPCO, INC.




|                              |              |        |                  |      |            |          |
|------------------------------|--------------|--------|------------------|------|------------|----------|
| UNIT                         | MODEL #      | SCALE  | DWG. #           | REV. | DATE       | SERIAL # |
| <b>EVAPORATIVE CONDENSER</b> | eco-PMC-1780 | N.T.S. | ECE124006-DRA-ST | -    | 12/13/2025 |          |

- NOTES:
1. (M)- FAN MOTOR LOCATION
  2. HEAVIEST SECTION IS UPPER SECTION
  3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING
  4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
  5. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
  6. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
  7. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
  8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm]

**FACE 1  
PLAN VIEW**



**FACE 1**



**FACE 2**

|                 |                        |                  |                        |                         |                       |                          |   |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|
| SHIPPING WEIGHT | 59030 lbs+ [26776] kg+ | OPERATING WEIGHT | 75990 lbs+ [34468] kg+ | HEAVIEST SECTION WEIGHT | 20860 lbs+ [9462] kg+ | NO. OF SHIPPING SECTIONS | 3 |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|