




UNIT	CONDENSER		EVAPCO, INC. 	DWG. #	WB3TM3606-DRC-ST	REV.
MODEL #	eco-ATC-1032A	SCALE NTS		SERIAL #		DATE 1/8/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]



SHIPPING WEIGHT 42100 lbs+ [19100] kg+ OPERATING WEIGHT 59820 lbs+ [27135] kg+ HEAVIEST SECTION WEIGHT 17400 lbs+ [7895] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: SLR