
UNIT	CONDENSER	
MODEL #	eco-ATC-884A	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # REV. WB3121812-DRC-ST DATE_{11/26/2025} SERIAL #


FACE D


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]



FACE A

FACE C





DRAWN BY: SLR NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 38550 lbs+ [17490] kg+ 34630 lbs+ [15710] kg+ 49350 lbs+ [22385] kg+ WEIGHT WEIGHT WEIGHT