


UNIT	CONDENSER		EVAPCO, INC. 	DWG. #	WB3122812-DRC-ST	REV.
MODEL #	eco-ATC-1149A	SCALE NTS		SERIAL #		DATE 1/23/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]



FACE B



DWG. # WB3122813 DRG ST


REV.

SERIAL :

DATE 1/23/2026


FACE B

FACE C



FACE D

FACE A



FACE A

SHIPPING WEIGHT 61020 lbs+ [27680] kg+ OPERATING WEIGHT 77880 lbs+ [35330] kg+ HEAVIEST SECTION WEIGHT 27450 lbs+ [12455] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: SLR