EVAPCO, INC. UNIT MODEL # REV. SERIAL # **CONDENSER** N.T.S. EG241804-DRA-ST eco-ATC-1021A 11/22/2025 ACCESS DOOR NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE 24'-1 1/8" [7344] FOR PRE-FABRICATION OF CONNECTING FACE 2 7. VENT PROVIDED ON CLOSED CIRCUIT COOLERS **PLAN VIEW** ONLY ACCESS DOOR FACE 1 7 [178] 69 1/4 _{*} 1759] (4) 4 [100] BFW 36 3/8 _{*} 924] 13 3/4 _{*} [349] (4) 1/2 [15] FPT VENT (CLOSED CIRCUIT COOLERS ONLY) - INLET OUTLET 15'-9 3/8" [4810] (4) 4 [100] BFW [152] 98 1/4 [2496] 56 [1422] 17 [431] - (2) 2 [50] MPT MAKE-UP (2) 3 [80] MPT DRAIN 3 5/8 [92] 136 3/4 3473] - (2) 3 [80] MPT OVERFLOW 137 3/4 3499] 142 [3607] 18'-0" 5486] FACE 1 FACE 2 SHIPPING OPERATING HEAVIEST SECTION NO. OF SHIPPING SECTIONS 39440 lbs+ [17890] kg+ 58820 lbs+ [26685] kg+ 15800 lbs+ [7170] kg+ WEIGHT WEIGHT WEIGHT