INIT	CONDENSER				*	DWG. # EG091104-DR0	C-ST REV
IODEL #	eco-ATC-239A	SCALE NTS	EVAPC	O, INC.	vapco	SERIAL #	DATE _{12/14/2025}
2. HEAVI 3. MPT I FPT D BFW I GVD I FLG D PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. *-APPI FOR F PIPINO 7. 3/4" [1 RECO 8. DIMEN	AN MOTOR LOCATION IEST SECTION IS UPPER SI DENOTES MALE PIPE THRE DENOTES FEMALE PIPE THRE DENOTES BEVELED FOR W DENOTES GROOVED DENOTES PLAIN END WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSOR -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 ROXIMATE DIMENSIONS DO PRE-FABRICATION OF CONI G 9mm] DIA. MOUNTING HOLI MMENDED STEEL SUPPOR NSIONS LISTED AS FOLLOV ENGLISH FT-IN METRIC [mm]	AD READ PELDING JDE Y DRAWINGS) B44 kPa] D NOT USE NECTING ES. REFER TO RT DRAWING.		FAC PLAN VIE		FACE C ACCESS DOOR	FACE D
	1'-9 3/8"	4'-3/4"	2'-2 3/8" #		1'-7/8" [327]	FACE A	
	(2) 4" [100] PE 1'-0" * [305] *	4'-3/4" *	2'-2 3/8" * [670] * [1930] FRIGIN REFRIG OUT	'-7 7/8" 3248]			
	(2) 4" [100] PE 2" [50] MPT MAKE-UP 1'-11 1/8" [587]	27 [50]	6" * [152] * 4'-3 7/8" [1318]				
	3"	- 2" [50] MPT DRAIN - 5 1/4" - [133] - 4 1/4" - [108] - 5'-7 1/4" - [1708] - 8'-5 1/2" - [2578]	3" [80] MPT OVERFLOW	1 [3	'-3" 881]	10'-5 1/2"	
SHIPPING	9260 lbs+ [42	FACE B	RATING 12600 lbs+ [5720] k	rg+ HEAVIEST SECTION WEIGHT	7620 lbs+ [3460] kg+	FACE A NO. OF SHIPPING SECTIONS	2 DRAWN BY: JLG

HEAVIEST SECTION WEIGHT

SHIPPING WEIGHT

OPERATING WEIGHT