UNIT	CONDENSER	
MODEL #	eco-ATC-225A	SCALE NTS

EVAPCO, INC. Evapco




DWG. # REV. EG091204-DRC-ST DATE<sub>12/14/2025</sub> SERIAL #

## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN METRIC [mm]

## **FACE C**



## **FACE A**





DRAWN BY: JLG NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 9710 lbs+ [4405] kg+ 7840 lbs+ [3560] kg+ 13630 lbs+ [6185] kg+ WEIGHT WEIGHT WEIGHT