UNIT CONDENSER		NO AVONCO	DWG. # CW4C071806-DRA-ST	REV.
10DEL # eco-ATC-433A SCALE N	EVAPCO, I	NC. evapeo	SERIAL #	DATE _{12/14/2025}
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER T RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	FACE PLAN VIE	ACCESS DOOR ACCESS DOOR	ACE C ACCESS DO ACCES D	FACE D
1'-9 3/8" 1'-7 1/2" * (2) 4'[100] PE REFRIG COMMAKE-UP 2" [50] MPT DRAIN 1'-11 1/8" [587] 3" [132] 4 1/4" [107] 5'-3 5/8" [1616] 7'-4" [2235] FACE B	12'-1/2" [36/0] 5 1/4" *		18'-0" 5486]	
SHIPPING 16460 lbs+ [7470] kg+ WEIGHT	OPERATING 19690 lbs+ [8935] kg+	HEAVIEST SECTION 13440 lbs+ [6100] kg+		RAWN BY: TAM