UNIT CONDENSER			EVAPCO, INC. Evapeo				DWG. # CW4C071808-DRA-S	REV	
MODEL #	eco-ATC-505A	SCALE NTS	T EVAI	PCO, 1	NC.		SERIAL #	DATE 12/14/2025	
2. HEAVIE 3. MPT DE FPT DE BFW D GVD DI FLG DE PE DEN 4. +UNIT N ACCES 5. MAKE-I 20 psi N 6. *-APPR FOR PR FOR PR FOR PR 7. 3/4" [19 RECON	N MOTOR LOCATION EST SECTION IS FAN/CASIR ENOTES MALE PIPE THRE/ENOTES FEMALE PIPE THRE/ENOTES BEVELED FOR WIENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUSORIES (SEE ACCESSORY UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3] COXIMATE DIMENSIONS DO RE-FABRICATION OF CONNIMM] DIA. MOUNTING HOLE MENDED STEEL SUPPOR' SIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	DE / DRAWINGS)  44 kPa]  NOT USE IECTING  ES. REFER TO T DRAWING.		FA PLAN VI	CE B EW	ACCESS DOOR		ESS DOOR  FACE D	
2" [50] N MAKE 2" [50] N DR. 1'-11 [ 58	-UP MPT AIN  1/8"  3"	REFRIG IN REFRIG OUT	2'-11 3/8" [ 899 ] - 1'-10 7/8" * 4'-8 3/8" [ 1432 ] - 5 1/4" * [ 133 ] * 5'-1/4" [ 1530 ] - 3" [80] MPT OVERFLOW	-8" 61]			18'-0" 5486		
SHIPPING	FAC		OPERATING 22020 Ibou [10405] kg i		HEAVIEST SECTION		ACE A	NO OF CHARDANG CECTIONS DRAWN BY:	
WEIGHT	19610 lbs+ [88	95] kg+	WEIGHT 22930 lbs	s+ [10405] kg+	WEIGHT	16590 lbs+ [7530] kg+	NO. OF SHIPPING SECTIONS 2	TAM	