UNIT	CONDENSER	
MODEL #	eco-ATC-1020A	SCALE NTS

EVAPCO, INC. Evapeo

HEAVIEST SECTION

WEIGHT

DWG. # EG123604-DRC-ST REV.
SERIAL # DATE 11/22/2025

DRAWN BY:


NO. OF SHIPPING SECTIONS


NOTES:

SHIPPING

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]






39440 lbs+ [17890] kg+

OPERATING

WEIGHT

58820 lbs+ [26685] kg+



15800 lbs+ [7170] kg+