JNIT CONDENSER			EVAD	DWG. #	DWG. # WB3124010-DRC-ST			
IODEL #	eco-ATC-1642A	SCALE NTS	EVAP	CO, INC	evapco	SERIAL #		DATE 11/27/2025
2. HÉAVIE 3. MPT DE FPT DE BFW DI GVD DE FLG DE PE DEN 4. +UNIT V ACCES 5. MAKE-L 20 psi M 6. *-APPR FOR PF PIPING 7. 3/4" [19 RECOM	N MOTOR LOCATION EST SECTION IS UPPER SECENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WE ENOTES FLANGE NOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUE SORIES (SEE ACCESSORY UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [34 OXIMATE DIMENSIONS DO RE-FABRICATION OF CONN mm] DIA. MOUNTING HOLE MENDED STEEL SUPPORT SIONS LISTED AS FOLLOWS ENGLISH FT-IN METRIC [mm]	ID EAD ELDING  DE DRAWINGS)  44 kPa] NOT USE ECTING S. REFER TO DRAWING.	<u>PLAN</u>	FACE B VIEW	ACCESS DOOR	CE C	ACCESS DOOR	FACE D
	1		[ 7"]	1'-3 1/4"		T		
3	3'-3 1/4" *	3'-3/8" * [ 924] *	9'-8 5/8" [ 2964] 16'-10 7/8" [ 5153]		(4)		(m)	
2'-1 1/4' [ 643 ]	[50] MPT — MAKE-UP — — — — — — — — — — — — — — — — — — —	6" [154]	* 7'-2 1/4" [ 2189]					<u> </u>
[	[ 92 ] — 5 1/4" — [ 133 ] — 4 1/4" — [ 108 ] — 7'-2" — [ 2184 ] —	(2) 3" [80] M OVERFLOW	IPT	2! 1/2"		2 1/2" [ 64]		2' 1/2"
	11'-10" [ 3607] <b>FACE B</b>			2'-1/2" -		'-2 1/2"  2256]   CE A	-	2'-1/2" [ 622 ]