UNIT	CONDENSER			Ī
MODEL #	eco-ATC-397A	SCALE	NTS	1


EVAPCO, INC. Evapeo

DWG.#	CW4C071410-DRA-ST	REV	-
SERIAL#		DATE:	10/27/2025

## NOTES

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]







**FACE C** 

FACE D

**FACE A** 



**FACE B** 



FACE A

 
 SHIPPING WEIGHT
 17060 lbs+ [7740] kg+
 OPERATING WEIGHT
 19580 lbs+ [8885] kg+
 HEAVIEST SECTION WEIGHT
 14870 lbs+ [6745] kg+
 NO. OF SHIPPING SECTIONS
 DRAWN BY: JLG