NIT CONDENSER		EVAPCO, INC. evapco			DWG. # WB3243610-DRC-ST	REV.	
MODEL #	eco-ATC-2696A	SCALE NTS	EVAPCO,	INC.		SERIAL #	DATE 11/3/2025
2. HÉAVIE 3. MPT DE FPT DE BFW DI GVD DE FLG DE PE DEN 4. +UNIT V 20 psi N 6. *-APPR FOR PF FOR PF FOR PF 7. 3/4" [19 RECOM	N MOTOR LOCATION EST SECTION IS UPPER SEC- ENOTES MALE PIPE THREA NOTES FEMALE PIPE THREA NOTES BEVELED FOR WE ENOTES GROOVED NOTES FLANGE IOTES PLAIN END WEIGHT DOES NOT INCLUD SORIES (SEE ACCESSORY JP WATER PRESSURE IIN [137 kPa], 50 psi MAX [34 OXIMATE DIMENSIONS DO RE-FABRICATION OF CONNI- mm] DIA. MOUNTING HOLES IMENDED STEEL SUPPORT SIONS LISTED AS FOLLOWS ENGLISH FT-IN METRIC [mm]	E DEAD LDING E DRAWINGS) 4 kPa] NOT USE ECTING S. REFER TO DRAWING.	PLAN	FACE B VIEW	FACE	(4) ACCESS DOOR	FACE D
2'-1 1/ ² [643] 1'- [43	(8) 4" [100] PE	11'-4 MPT 11'-4 (34: 7:4: (34:	9'-8 5/8" [2964] 17'-10 7/8" [5458] [154] 8'-2 1/4" [2494] 3/4"	1'-3 1/4" [387]		1'-11 1/8" _ _ [587]	-

FACE B

36'-2 1/2" [11036] FACE A