CLOSED CIRCUIT COOLER MODEL# ESW4 12-26L18-SF

EVAPCO, INC. EVAPCO



WX412182412F-DRA-ST

12/14/2025

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HÉAVIEST SECTION IS COIL SECTION

3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING


6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]


8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING




SERIAL#



FACE A



NTS



SHIPPING 34820 lbs+ [15795] kg+ WEIGHT

OPERATING WEIGHT

51390 lbs+ [23315] kg+

HEAVIEST SECTION WEIGHT

28110 lbs+ [12755] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

AWT