CLOSED CIRCUIT COOLER	EVADOO :	TNO Proposition	DWG.# WX41218X3604P-DRA-ST	REV -
MODEL# ESW4 12-32J18X-LP SCALE NTS	EVAPCO,	INC. evapeo	SERIAL#	DATE: 11/5/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPI 9. COIL CONNECTIONS LOCATED ON FACES B A	(2) 4" [100] BFW FLUID IN WG ND D * 2'-8"	FACE B PLAN VIEW (2) 4" [100] BFW FLUID OUT * 1'-0" [305] FACE 4'-7" * 2'-3 3/8" [695]		ACE D
2" [50] MPT MAKE-UP 3" [80] MPT DRAIN 2'-4" [711] 4" [107] 5 1/4" [132] 11'-10" [3607] FACE B	3" [80] MPT OVERFLOW 1'-7 3/8" [492] 4'-9 5/8" [1464]	(2)1/2" [15] FPT VENT 2'-1" 18 [635]	(M) ACCESS DOOR 9'-3'	1/4" [387] 7/8" [2843] 17'-11 1/8" [5466] 1/4" [2623]
SHIPPING WEIGHT 20460 lbs+ [9285] kg+ OPER WE	31390 lbs+ [14240] kg+	HEAVIEST SECTION 13070 lbs+ [5930] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT