DWG. # REV. UNIT **CONDENSER** CW4C071210-DRA-ST EVAPCO, INC. EVAPCO DATE<sub>12/14/2025</sub> MODEL # SCALE SERIAL # NTS eco-ATC-337A NOTES: **FACE C** 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD ACCESS DOOR BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **FACE B FACE D** 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING **PLAN VIEW** 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm] **FACE A** 1'-2" [ 356 ] 1'-9 3/8' [ 543 ] 1'-10 7/8" \* [ 581 ] (2) 4" [100] PE REFRIG IN 5'-3 7/8' [ 1622 ] 12'-7 1/8" [ 3839 ] 2'-10 1/2" \* (2) 4" [100] PE REFRIG OUT -0  $\bigcirc$ 2" [50] MPT MAKE-UP 2" [50] MPT DRAIN 4'-3 7/8' [ 1318 ] 1'-11 1/8" [587 ] 1'-3" [ 381 ] 3" [ 76 ] 3" [80] MPT OVERFLOW **FACE B FACE A** NO. OF SHIPPING SECTIONS DRAWN BY: **SHIPPING** OPERATING HEAVIEST SECTION 14750 lbs+ [6695] kg+ 16960 lbs+ [7695] kg+ 12850 lbs+ [5830] kg+ TAM

WEIGHT

WEIGHT

WEIGHT