DWG. # REV. UNIT **CONDENSER** CW4C071210-DRA-ST EVAPCO, INC. EVAPCO DATE_{12/13/2025} MODEL # SCALE SERIAL # NTS eco-ATC-352A NOTES: **FACE C** 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD ACCESS DOOR BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **FACE B FACE D** 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING **PLAN VIEW** 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm] **FACE A** 1'-2" [356] 1'-9 3/8' [543] 1'-10 7/8" * [581] (2) 4" [100] PE REFRIG IN 5'-3 7/8' [1622] 12'-7 1/8" [3839] 2'-10 1/2" * (2) 4" [100] PE REFRIG OUT -0 \bigcirc 2" [50] MPT MAKE-UP 2" [50] MPT DRAIN 4'-3 7/8' [1318] 1'-11 1/8" [587] 1'-3" [381] 3" [76] 3" [80] MPT OVERFLOW **FACE B FACE A**

HEAVIEST SECTION

WEIGHT

12910 lbs+ [5860] kg+

SHIPPING

WEIGHT

OPERATING

WEIGHT

17020 lbs+ [7725] kg+

14810 lbs+ [6720] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

TAM