UNIT CONDENSER						DWG. # CW4C072406-DRA-ST REV		
10DEL #	eco-ATC-595A	SCALE NTS		APCO, II	AC. evapeo	SERI		DATE _{12/14/2025}
2. HEAVIE 3. MPT DI FPT DE BFW D GVD DI FLG DE PE DEN 4. +UNIT 20 psi N 6. *-APPR FOR PI FOR PI 7. 3/4" [19 RECON	IN MOTOR LOCATION EST SECTION IS FAN/CASIN ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUE ISORIES (SEE ACCESSORY UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [34 COXIMATE DIMENSIONS DO RE-FABRICATION OF CONNI COMMINICATION OF CONN	DEAD LDING DE DRAWINGS) 4 kPa] NOT USE ECTING 5. REFER TO DRAWING.		FACE B PLAN VIEW	ACCESS DOOR FAC	CE A	ACCESS DOOR	FACE D
(2) 2" [50] MAKI (2) 2" [50] 1'-11 1 [587	1'-7 1/2" * (4) 4' [100] PE [495] * (4) 4' [100] PE DE-UP DRAIN	REFRIG IN REFRIG OUT 1'-3 [38]	2'-11 3/8" 1'-10 7/8" *		11'-11 3/4" [3651]	2 [-2" 66]	1/2" 641	1'-5 1/8" [435]
SHIPPING WEIGHT	30420 lbs+ [1380	00] kg+	OPERATING 330 WEIGHT	30 lbs+ [14985] kg+	HEAVIEST SECTION 11580 lbs+ [5255] kg]+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: TAM