UNIT CLOS	ED CIRCUIT COOLER				DWG. # WX41218X2406P-DRA-S1	REV _
	SCALE	<del>.  </del> EVAPO	CO, INC.	evapco	SERIAL #	DATE: 11/25/2025
NOTES: 1. (M)- FAN 2. HEAVIE 3. MPT DEI BFW DE GVD DE FLG DEI 4. +UNIT V ACCESS 5. 3/4" [19N REFER SUPPOR 6. MAKE-U 20 psi M7. DIMENS ENGI [MET 8. * - APPR FOR PR	I MOTOR LOCATION ST SECTION IS COIL SECTION NOTES MALE PIPE THREAD NOTES FEMALE PIPE THREAD NOTES BEVELED FOR WELDING NOTES GROOVED NOTES FLANGE VEIGHT DOES NOT INCLUDE SORIES (SEE ACCESSORY DRAW MM] DIA. MOUNTING HOLES. TO RECOMMENDED STEEL RT DRAWING P WATER PRESSURE IN [137 kPa], 50 psi MAX [344 kPa] IONS LISTED AS FOLLOWS: LISH FT-IN RIC] [mm] ROXIMATE DIMENSIONS DO NOT LEFABRICATION OF CONNECTING DINNECTIONS LOCATED ON FACES	NGS)  (2) 4" [100] BFW FLUID IN  SE PIPING	(2) 4" [100] BFW FLUID OUT  * 1'-7 1/2"  * 4'-7" [1397]	FAC	<u>E</u>	ACE D
2'-4	2" [50] MPT MAKE-UP 3" [80] MPT DRAIN 4" [711] 4 1/4" [107] 5 1/4" [132] 11'-1 [360]		(2)1/2" [15] FPT VENT -	1" 18'- 35] FAC	(M)   ACCESS   DOOR   8'-3	3 1/4" [387] 7/8" [2538] 17'-6 5/8" [5351] 3/4" [2813] 1/2" 99]
SHIPPING WEIGHT	22190 lbs+ [10070] kg+	OPERATING 33920 lbs+ [15390]	kg+ HEAVIEST SECTION WEIGHT	15370 lbs+ [6975] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT