CLOSED CIRCUIT COOLER	FV/ADCO	TNC Evança	DWG. # WX41218X3612P-DRA-ST
MODEL# ESW4 12-36J18X-LP SCALE NTS	EVAPCO,	INC. evapeo	SERIAL # DATE: 11/11/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE	(2) 4" [100] BFW — FLUID IN	FACE B PLAN VIEW - (2) 4" [100] BFW FLUID OUT * 3'-6" [1067]	ACE C FACE D
9. COIL CONNECTIONS LOCATED ON FACES B A	ND D * 2'-8"	* 2'-3 3/8" [695] [1397]	7" [178] 1'-3 1/4" [387] (M) 1 ACCESS DOOR
2" [50] MPT	3" [80] MPT OVERFLOW	(2)1/2" [15] FPT VENT	9'-3 7/8" [2843] 20'-5 1/8" [6228]
2'-4" [711] 4" [101] 4 1/4" [107] 5 1/4" [132] 11'-10" [3607] FACE B	1'-7 3/8" [492] 4'-9 5/8" [1464]	[635]	18'-0" 2'-3 1/2" [699] ACE A
	43820 lbs+ [19880] kg+	HEAVIEST SECTION 22300 lbs+ [10120] kg+	NO. OF SHIPPING SECTIONS 2 DRAWN BY: AWT