CLOSED CIRCUIT COOLER MODEL# ESW4 12-35I12-LF NTS NOTES: 1. (M)- FAN MOTOR LOCATION

EVAPCO, INC. Evapeo



WX412123610F-DRA-ST SERIAL# DATE: 11/9/2025

- 2. HEAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]

SHIPPING

WEIGHT

8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

21870 lbs+ [9925] kg+


OPERATING

WEIGHT

32030 lbs+ [14530] kg+

FACE C

FACE B PLAN VIEW




FACE D

NO. OF SHIPPING SECTIONS

DRAWN BY:

AWT

FACE A



HEAVIEST SECTION

WEIGHT

16410 lbs+ [7445] kg+