

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 12-44L12-SP

EVAPCO, INC.



DWG. # WX412124808P-DRA-ST


REV -

SERIAL #

DATE: 2/19/2026

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING



FACE B


FACE B
PLAN VIEW

FACE C



FACE D

FACE A



FACE A

SHIPPING
WEIGHT

17280 lbs+ [7840] kg+

OPERATING
WEIGHT

25540 lbs+ [11585] kg+

HEAVIEST SECTION
WEIGHT

11160 lbs+ [5060] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT