

UNIT CLOSED CIRCUIT COOLER  
MODEL # ESW4 12-26L12-LF

SCALE NTS

EVAPCO, INC.




DWG. # WX412122412F-DRA-ST

REV -  
SERIAL #  
DATE: 2/10/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
8. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

FACE C




FACE B  
PLAN VIEW



FACE B

FACE D

FACE A



FACE A

SHIPPING  
WEIGHT

23730 lbs+ [10765] kg+

OPERATING  
WEIGHT

34680 lbs+ [15735] kg+

HEAVIEST SECTION  
WEIGHT

18610 lbs+ [8445] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT