CLOSED CIRCUIT COOLER			EVAPCO,	TNC E	evapco	DWG.# WX409183610P-DRA-S	
MODEL #	ESW4 9-35J18-LP	SCALE NTS	LVAI CO,			SERIAL#	DATE: 11/4/2025
2. HEAV 3. MPT I FPT D BFW I GVD I FLG D 4. +UNIT ACCE 5. 3/4" [1] REFE SUPP 6. MAKE 20 psi 7. DIMEI	AN MOTOR LOCATION IEST SECTION IS COIL SEC DENOTES MALE PIPE THRE DENOTES FEMALE PIPE THI DENOTES BEVELED FOR W DENOTES GROOVED DENOTES FLANGE WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSOR 9MM] DIA. MOUNTING HOL R TO RECOMMENDED STE ORT DRAWING 1-UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [ NSIONS LISTED AS FOLLON	EAD READ VELDING  UDE RY DRAWINGS) ES. EL  [344 kPa]	(2) 4" [100] BFW FLUID IN	FACE B PLAN VIEW  (2) 4" [100] BFW FLUID OUT -* 2'-10 1/2" [876]		CE C	□ FACE D
EN [ME 8. * - AP FOR F	IGLISH FT-IN ETRIC] [mm] PROXIMATE DIMENSIONS I PRE-FABRICATION OF CON CONNECTIONS LOCATED (	DO NOT USE INECTING PIPIN	G	* 2'-2 3/8" [670] -* 2'-10 3/4" [883]	FAC	CE A	8'-3 1/4" [2522]
	2" [50] MPT — MAKE-UP — 2" [50] MPT — DRAIN — DRAIN — 2'-3" [686]		3" [80] MPT OVERFLOW	(2)1/2" [15] FPT VENT			18'-4 7/8" [5612] 10'-1 5/8" [3090]
	3 3/8" [86] 4 1/4" [107] 5 1/4" [132]	8'-5 1/2" [2578] FACE B	2'-5 5/8" [752]	2'-2 1/4" [667]		-0" 86] CE A	<u> </u>
SHIPPING WEIGHT	22200 lbs+ [10070] k	kg+ OPERA WEIG	TING 31440 lbs+ [14265] kg+	HEAVIEST SECTION WEIGHT	15430 lbs+ [7000] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT