CLOSED CIRCUIT COOLER	FVΔPCΩ	INC. Evapeo	DWG. # WX409183612P-DRA-S	0.475
MODEL# ESW4 9-36I18-LP SCALE NTS			SERIAL#	DATE: 10/29/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS:	(2) 4" [100] BFW FLUID IN	FACE B PLAN VIEW (2) 4" [100] BFW FLUID OUT _* 3'-6" [1067]	FACE C (M)	FACE D
ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPIN 9. COIL CONNECTIONS LOCATED ON FACES B AN	IG O	* 2'-2 3/8" [670]	FACE A	_[1'-0 7/8" [327]
(M)	* 2'-8" [813] FACE B & D COIL CONNECTION	* 2'-10 3/4" [883]	ACCESS ACCESS DOOR DOOR	8'-3 1/4" [2522]
		(2)1/2" [15] FPT VENT		19'-0 3/8" [5802]
2" [50] MPT — MAKE-UP O	3" [80] MPT OVERFLOW	VENT		10'-9 1/8" [3281]
2'-3" [686]			0 0 0 0 0	
3 3/8" [86] 4 1/4" [107] 5 1/4" [132] 8'-5 1/2"	2'-5 5/8" [752]	2'-2 1/4" [667]	18'-0"	
[2578] FACE B				
SHIPPING WEIGHT 23670 lbs+ [10740] kg+ OPER WEI	ATING 33510 lbs+ [15200] kg+	HEAVIEST SECTION 17180 lbs+ [7795]	kg+ NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT