

UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 12-22M12-SP

EVAPCO, INC.




DWG. # WX412122404P-DRA-ST

REV -
SERIAL #
DATE: 1/19/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING




FACE B
PLAN VIEW

FACE D



FACE B



FACE A

SHIPPING
WEIGHT

13340 lbs+ [6055] kg+

OPERATING
WEIGHT

20560 lbs+ [9330] kg+

HEAVIEST SECTION
WEIGHT

8130 lbs+ [3690] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT