UNIT CLOS	ED CIRCUIT COOLER	Т	EV/4 DCO	TNIC	avanca *	DWG. # WX409123612P-DRA-ST	REV _
		NTS	EVAPCO,	INC.		SERIAL#	DATE: 10/27/2025
2. HÉAVIE: 3. MPT DE FPT DEN BFW DE GVD DE FLG DEN 4. +UNIT W ACCESS 5. 3/4" [19M REFER SUPPOF 6. MAKE-U 20 psi M 7. DIMENS ENGL	I MOTOR LOCATION ST SECTION IS COIL SECTION NOTES MALE PIPE THREAD NOTES FEMALE PIPE THREAD NOTES GROOVED NOTES GROOVED NOTES FLANGE /EIGHT DOES NOT INCLUDION SORIES (SEE ACCESSORY IN MI) DIA. MOUNTING HOLES TO RECOMMENDED STEEL RT DRAWING P WATER PRESSURE IN [137 kPa], 50 psi MAX [34-10) LISTED AS FOLLOWS LISH FT-IN RIC] [mm]	O AD LDING E DRAWINGS)		FACE B PLAN VIEW	FACE C	FACE D	
8. * - APPR	COXIMATE DIMENSIONS DO E-FABRICATION OF CONNE				FACE A	<sub>[</sub> -1'-0 7/8" [327]	
	(M) * 2'-8" [813]				(W)	(ACCESS) (DOOR) 8'-3 1/4" [2522]	
	4" [100] BFW — FLUID IN 2" [50] MPT — MAKE-UP		4" [100] BFW FLUID OUT  3" [80] MPT OVERFLOW  -* 3'-6" [1067]	1/2" [15] FPT VENT		18'-4 3/	8" [5599]
	2" [50] MPT — DRAIN 2'-3" [686]	8				0 0 [3077]	
	3 3/8" [86] 4 1/4" [107]		2'-2 3/8" [670] 1'-6 3/8" [465] 2'-5 5/8" [752]	2'-1' [635	"11'-11 3/4" [3651]		_
	5 1/4"	8'-5 1/2" [2578] FACE B	* 2'-10 3/4" [883]		FACE A		
SHIPPING WEIGHT	17030 lbs+ [7725] kg+	- OPERATING WEIGHT	<sup>3</sup> 24290 lbs+ [11020] kg+	HEAVIEST SECTION WEIGHT	13170 lbs+ [5975] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT