

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 9-45J6-LP

EVAPCO, INC.



DWG. # WX409064810P-DRA-ST


REV -

SERIAL #

DATE: 1/20/2026

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING



FACE B


PLAN VIEW

FACE C



FACE D

FACE A



FACE A

SHIPPING
WEIGHT

8740 lbs+ [3965] kg+

OPERATING
WEIGHT

12020 lbs+ [5455] kg+

HEAVIEST SECTION
WEIGHT

6180 lbs+ [2805] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT