



UNIT **CLOSED CIRCUIT COOLER**
MODEL # **ESW4 12-35I12-LF** SCALE **NTS**

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL
SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING PIPING




FACE B



FACE B



FACE D



FACE A

SHIPPING WEIGHT 21870 lbs+ [9925] kg+ OPERATING WEIGHT 32030 lbs+ [14530] kg+ HEAVIEST SECTION WEIGHT 16410 lbs+ [7445] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: AWT