| CLOSED CIRCUIT COOLER | E)/4 DGO | | DWG. # WX41218X4812P-DRA-ST REV - |
|--|---|--|--|
| ESW4 12-46K18X-LP SCALE NTS | EVAPCO, | INC. Evapeo | SERIAL# DATE: 11/20/2025 |
| NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPI | (2) 4" [100] BFW FLUID IN | FACE B PLAN VIEW (2) 4" [100] BFW FLUID OUT * 3'-6" [1067] | CE C FACE D |
| 2" [50] MPT MAKE-UP 3" [80] MPT DRAIN 2'-4" [711] 4 1/4" [107] 5 1/4" [132] 11'-10" [3607] FACE B | * 2'-8" [813] FACE B & D COIL CONNECTION: 3" [80] MPT OVERFLOW -1'-7 3/8" [492] 4'-9 5/8" [1464] | (2)1/2" [15] FPT VENT 2'-1" 18 [54 | 7" [178] 1'-3 1/4" [387] (M) 1ACCESS (DOOR 10'-3 7/8" [3148] 21'-5 1/8" [6532] 3'-0" 486] 2'-3 1/2" [699] |
| SHIPPING WEIGHT 30450 lbs+ [13815] kg+ OPER WE | RATING 44580 lbs+ [20225] kg+ | HEAVIEST SECTION 22300 lbs+ [10120] kg+ | NO. OF SHIPPING SECTIONS 2 DRAWN BY: AWT |