

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 9-34I12-SP

**EVAPCO, INC.**




DWG. # WX409123608P-DRA-ST

REV -  
SERIAL #  
DATE: 2/12/2026

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
- \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING



**FACE B**


**PLAN VIEW**

**FACE C**



**FACE D**

**FACE A**



**FACE A**

SHIPPING  
WEIGHT

13790 lbs+ [6260] kg+

OPERATING  
WEIGHT

19990 lbs+ [9070] kg+

HEAVIEST SECTION  
WEIGHT

10080 lbs+ [4570] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT