CLOSED CIRCUIT COOLER EVAPCO, INC. Evapeo WX409093612P-DRA-ST MODEL# SERIAL# ESW4 9-36I9-LP 10/29/2025 NTS NOTES: 1. (M)- FAN MOTOR LOCATION **FACE C** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD (M) FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING ==== **GVD DENOTES GROOVED** FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. **FACE B FACE D** REFER TO RECOMMENDED STEEL **PLAN VIEW** SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm] **FACE A** 8. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING <sup>1'-0</sup> 7/8" [327] L(M) ACCESS \* 2'-8" [813] 8'-3 1/4" [2522] 4" [100] BFW FLUID OUT 4" [100] BFW FLUID IN 18'-1 3/8" [5523] 3" [80] MPT **OVERFLOW** 1/2" [15] FPT 2" [50] MPT -\* 3'-6" [1067] MAKE-UP 2" [50] MPT 9'-10 1/8" [3001] DRAIN 2'-3" [686]-L\* 2'-2 3/8" [670] 3 3/8" [86]-L1'-6 3/8" [465] 2'-0 1/2" 8'-11 1/2" [621] [2731] 2'-5 5/8" 4 1/4" [752] [107] \* 2'-10 3/4" 5 1/4" [883] [132] 8'-5 1/2" [2578] **FACE B FACE A** NO. OF SHIPPING SECTIONS DRAWN BY: 13500 lbs+ [6125] kg+ OPERATING 18830 lbs+ [8545] kg+ SHIPPING HEAVIEST SECTION 10440 lbs+ [4735] kg+ **AWT** WEIGHT WEIGHT WEIGHT