CLOSED CIRCUIT COOLER EVAPCO, INC. Evapeo WX409124806P-DRA-ST MODEL# SERIAL# ESW4 9-43J12-SP 10/16/2025 NTS NOTES: 1. (M)- FAN MOTOR LOCATION **FACE C** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD (M) FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING ==== **GVD DENOTES GROOVED** FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. **FACE B FACE D** REFER TO RECOMMENDED STEEL **PLAN VIEW** SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm] **FACE A** 8. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING −1'-0 7/8" [327]  $\lceil (\overline{M}) \rceil$ \* 2'-8" ACCESS [813] (DOOR 9'-3 1/4" [2826] 4" [100] BFW 4" [100] BFW 17'-5 7/8" [5332] FLUID IN FLUID OUT 2" [50] MPT 3" [80] MPT MAKE-UP 1/2" [15] FPT OVERFLOW VENT 2" [50] MPT -\* 1'-7 1/2" [495<u>]</u> DRAIN 8'-2 5/8" [2506] 2'-3" [686]-L\* 2'-2 3/8" [670] 3 3/8" [86]-<sup>1</sup>-6 3/8" [465] 2'-1" 11'-11 3/4" [635] [3651] 2'-5 5/8" 4 1/4" [752] [107] \* 2'-10 3/4" 5 1/4" [883] [132] 8'-5 1/2" [2578] **FACE A FACE B** NO. OF SHIPPING SECTIONS DRAWN BY: SHIPPING OPERATING 8590 lbs+ [3895] kg+ 12770 lbs+ [5795] kg+ 18450 lbs+ [8370] kg+ HEAVIEST SECTION **AWT** WEIGHT WEIGHT WEIGHT