					100	I nua "	Lasy
CLOSED CIRCUIT COOLER			EVAPCO, INC		evapco	DWG.# WX409124812P-DRA-ST	REV _
MODEL#	ESW4 9-46L12-LP	ITS	EVAPCO	, TIAC		SERIAL#	DATE: 11/24/2025
2. HEAV 3. MPT I FPT D BFW I GVD I FLG D 4. +UNIT ACCE 5. 3/4" [1] REFEL SUPP 6. MAKE 20 psi 7. DIMEN	AN MOTOR LOCATION IEST SECTION IS COIL SECTION DENOTES MALE PIPE THREAD DENOTES FEMALE PIPE THREAD DENOTES BEVELED FOR WELDING DENOTES GROOVED DENOTES FLANGE 'WEIGHT DOES NOT INCLUDE SSORIES (SEE ACCESSORY DRAW 9MM] DIA. MOUNTING HOLES. R TO RECOMMENDED STEEL ORT DRAWING -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [344 kPa] NSIONS LISTED AS FOLLOWS: GLISH FORM	NGS)		FACE B PLAN VIEW	FACE (M)	FACE D	
8. * - API	ETRIC] [mm] PROXIMATE DIMENSIONS DO NOT U PRE-FABRICATION OF CONNECTING				FACE A	1 1'-0 7/8" [327]	
FURF	RE-FABRICATION OF CONNECTING	PIPING					Ŧ
	(M) * 2'-8" [813]	-	4" [100] BFW		[,(M)]	ACCESS (DOOR) 9'-3 1/4" [2826]	
	4" [100] BFW FLUID IN 2" [50] MPT MAKE-UP		FLUID OUT - 3" [80] MPT OVERFLOW -* 3'-6" [1067]	1/2" [15] FP' VEN		19'-4 3	/8" [5904]
	2" [50] MPT DRAIN 2'-3" [686]					10'-1 1/8" [3077]	
	3 3/8" [86]	-	2'-5 5/8" [752]	2' [6	11'-11 3/4 35] [3651]	1	<u>.</u>
	[107] 5 1/4" [132] 8'-5 1/2 [2578 FACE]	* 2'-10 3/4" [883]		FACE A		
SHIPPING	17420 lbs+ [7905] kg+	OPERATIN WEIGHT	³ 24680 lbs+ [11195] kg+	HEAVIEST SECTION		NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT
WEIGHT	[]]	WEIGHT	- [1.19	WEIGHT	- []		/\V \ I